

## LATILUB 62-01M G/30

Self-lubricating product based on Polyamide 6 (PA6).  
Molybdenum dysulphide. Glass fibers.

PHYSICAL PROPERTIES	STANDARD	VALUE MEASURE UNITS
Density	ISO 1183	1.36 g/cm <sup>3</sup>
Linear shrinkage at moulding		
Longitudinal (0.078in/8,700psi)	ISO 294-4	0.004 ÷ 0.006 in/in
Transversal (0.078in/8,700psi)	ISO 294-4	0.004 ÷ 0.006 in/in
MECHANICAL PROPERTIES	STANDARD	VALUE MEASURE UNITS
CHARPY impact strength		
Unnotched, at +73°F	ISO 179-1eU	32.71 ft.lb/in <sup>2</sup>
Notched, at +73°F	ISO 179-1eA	4.21 ft.lb/in <sup>2</sup>
Tensile elongation		
At break (0.196 in/min), 73°F	ISO 527 (1)	3.0 %
Tensile strength		
At break (0.196 in/min), 73°F	ISO 527 (1)	23200 psi
Elastic modulus		
Tensile (speed 0.04 in/min), at 73°F	ISO 527 (1)	1280 kpsi

## LATILUB 62-01M G/30

Self-lubricating product based on Polyamide 6 (PA6).  
Molybdenum dysulphide. Glass fibers.

THERMAL PROPERTIES	STANDARD	VALUE MEASURE UNITS
<b>VICAT - Softening point</b>		
11 lb (heating rate 122°F/h)	ISO 306	410 °F
<b>HDT - Heat Deflection Temperature</b>		
66 psi	ISO 75	428 °F
264 psi	ISO 75	392 °F
FLAMMABILITY	STANDARD	VALUE MEASURE UNITS
<b>Flammability rating</b>		
0.059 in thickness	UL 94	HB
ELECTRICAL PROPERTIES	STANDARD	VALUE MEASURE UNITS
<b>Electrical resistivity</b>		
Surface	ASTM D 257	1E12 ohm
TRIBOLOGICAL PROPERTIES	STANDARD	VALUE MEASURE UNITS
<b>Wear Factor</b>	ASTM D 3702	31 10 <sup>-7</sup> mm <sup>3</sup> /(Nm)
<b>Friction Coefficient</b>		
static	ASTM D 1894	0.45
dynamic	ASTM D 1894	0.38

## LATILUB 62-01M G/30

Self-lubricating product based on Polyamide 6 (PA6).  
Molybdenum dysulphide. Glass fibers.

### MATERIAL - STORAGE

Sealed, undamaged packages has to be kept in dry storage facilities, providing they are also able to protect them from weather and accidental damages.

### HANDLING AND SAFETY

Detailed information about a safe treatment of the material are indicated in the "Material Safety Data Sheet" (MSDS) furnished with the first material supply. The MSDS may be also sent again in case of loss.

### PREDRYING CONDITIONS

At least 3 hours at 194 ÷ 212°F

These are the suggested conditions to reduce the moisture content to adequate levels. Temperature and drying time can be reduced by using vacuum ovens

### ACTUAL MELT TEMPERATURE

464 ÷ 536°F

The injection molding machine settings needed to obtain the suggested melt temperature will depend greatly on shot size and machine capacity, as well as other molding parameters such as: injection speed, screw RPM, back pressure, etc. On small machines, running short cycles, it is possible to use higher melt temperatures to improve plastification, fluidity and surface appearance, paying attention to any indication of material degradation.

### MOLD TEMPERATURE

158 ÷ 212°F

The mold temperature suggested above is the actual tool steel temperature. This can be significantly different from the tool settings, due to the cooling system efficiency and the accuracy of the temperature control on the tool.

### INJECTION SPEED

Medium

The advisable injection speed greatly depends on cavity geometry and injection molding machine size. The use of high injection speed can improve the surface appearance, but it can also cause outgassing and burn marks due to overheating through shear stress.

### REGRIND USAGE

The use of regrind is possible, but should be assessed on the basis of the project, moulding parameters, and type of grinding used. The effect of using regrind on material properties must be evaluated by the customer on its specific project and process. High percentages of regrind may cause a reduction in viscosity and fibre length, reducing mechanical properties, first resilience. According to UL guideline, up to 25% of regrind is permitted, without affecting the ratings of the yellow card. However, LATI suggests that no more of 15% of regrind is used.

### HOT RUNNER MOLDS

Hot runner moulds may be used when a very tight temperature control is assured.

## LATILUB 62-01M G/30

Self-lubricating product based on Polyamide 6 (PA6).  
Molybdenum disulphide. Glass fibers.

### TO AVOID

Shut-off nozzles and internally heated hot runners have to be avoided. In order to prevent any material degradation, over-dimensioned machines should be avoided.

### NOTES

**The products mentioned herein are not suitable for applications in contact with foodstuff or for potable water transportation, or for toy manufacturing. The products mentioned herein are not suitable for applications in the pharmaceutical, medical or dental sector.**

### APPROVALS

USA (UL): Product versions approved according UL recommendations are available.

### CONTACTS

**LATI Industria Termoplastici S.p.A.**

Via F. Baracca, 7 - I - 21040 VEDANO OLONA (VA)

Tel. +39-0332-409111 - Fax +39-0332-409260

[email: techserv@it.lati.com](mailto:techserv@it.lati.com)

<http://www.lati.com>

<http://lambda.lati.it>

Values shown are based on testing of injection moulded laboratory test specimens, conditioned according to the standard and represent data that fall within the standard range of properties for non-coloured material, if not otherwise specified. As they may be subject to variations, these values do not represent a sufficient basis for any part design and are not intended for use in establishing values for specification purposes. Properties of moulded parts can be influenced by a wide range of factors including, but not limited to, colorants, part design, processing conditions, post-treatment conditions, environmental conditions and usage of regrind during the moulding process. If data are explicitly indicated as provisional, range of properties has to be considered wider. This information and technical assistance are provided as a convenience for informational purposes only and are subject to change without notice. The customer shall always ensure that the latest release of technical information is at his own disposal. Lati S.p.A. extends no warranties or guarantee, including a warranty of merchantability of whatever use is made of the product, and make no representations as to the accuracy, suitability, reliability, completeness and sufficiency of the information provided, and assume no responsibility regarding the consequences of its use or for any printing errors. It is the customer's responsibility to inspect and test our products in order to determine to his own satisfaction whether they are suitable for his intended uses and applications or used in conjunction with third-party materials. This application-specific analysis shall at least include preliminary testing to determine the suitability for the customer's particular purpose from a technical as well as health, safety, and environmental standpoint. Such testing has not necessarily been done by us as the manner in which the customer uses and the purpose to which utilises our products are beyond our control. Lati S.p.A. does not accept and hereby disclaims liability for any damages whatsoever in connection with the use of or reliance on this information. No one is authorised to make any warranties, issue any immunities or assume any liabilities on behalf of Lati S.p.A., except in a writing signed by a specifically authorised Lati S.p.A. executive. Unless otherwise agreed in writing, the exclusive remedy for all claims is replacement of the product or refund of the purchase price at Lati's option, and in no event shall Lati S.p.A. be liable for special, consequential, incidental, punitive or exemplary damages. No information herein can be considered as a suggestion to use any product in conflict with intellectual property rights. Lati S.p.A. disclaims any liability that may be claimed for infringement or alleged infringement of patents. Unless specifically stated in writing, the products mentioned herein are not suitable for applications in the pharmaceutical, medical or dental sector, in contact with foodstuff or for potable water transportation. For any other issues Lati S.p.A. Conditions of Sales apply.